

LIFE SCIENCES

Product Information - FJ

"FJ" Digital Temperature Gauge

Introduction

The Anderson-Negele FJ Digital Temperature Gauge carries on the tradition of accurate and reliable electronic temperature indication, while incorporating many new features tailored to a growing industry.

This "next generation" product provides high accuracy temperature monitoring in an operator friendly simple to read design. The FJ also offers new options for remote mounting as well as high and low switches for critical applications where user-defined setpoints can be easily programmed.

The battery-operated version can be ordered with or without a secondary 100 ohm 3-wire RTD. The secondary RTD option is ideal for applications that require local indication, as well as remote recording. As only one vessel penetration is required, a cost savings can be realized.

The DC powered version supplies two (2) SPST low voltage contacts assigned to the adjustable setpoints. An optional remote relay module is available that provides SPDT relays rated 6 amps at 250 VAC.

All models feature simple field calibration for fine tuning to the plant reference standard. As such, the FJ makes a perfect and cost-effective replacement for any mechanical thermometer, from bi-metals to mercury-in-glass. With resolution to a tenth of a degree, the FJ takes the guesswork out of reading dials and mercury columns. And, because it's an Anderson-Negele Life Sciences Series, you get the added value of all 316 "L" electropolished wetted parts, customer specified permanent tagging, a certificate of calibration, and CMTRs with every unit at no additional cost.

Complete specifications and ordering information are available on the reverse. For additional information please visit us on the web at www.anderson-negele.com, or contact your local Authorized Anderson-Negele Distributor.



Features

- Models and fittings specifically designed for Pharmaceutical and Biotech applications
- Operates on field replaceable batteries; DC switching version available
- Large Liquid Crystal Display makes viewing easy and repeatable
- All models offer field calibration capability
- · All programming and adjustments behind tamper-resistant back plate

LIFE SCIENCES

2

Specifications Compliance: 3-A, NEMA 4X, IP-66 Internal Switch Rating: 1 amp at 24 VDC SPST Product Contact Material: Fitting & Probe: 316L SS Remote Relay Rating: 6 amp at 250 VAC SPDT Product Contact Finish: R_a max = 8 micro inches, Two "AA" 3.6VDC Thionyl Chloride Power: Electrpolished Lithium (Style 0,1,5) Non-Product Contact Surface: Housing - 304 SS 9-30V DC external supply (Style 2) Style 0,1,5: 12 month minimum Lens - Polysulfone Battery Life: 0 to 300°F (-18 to 150°C) Style 2: Externally powered Process Temp. Range: Units: Deg F and Deg C; field selectable Vibration: 10 to 60 Hz, 2g Resolution: 0.1°F or °C Warranty: 2 vear Accuracy: ± 0.75°F (± 0.4°C) Secondary Output: Additional 100 ohm RTD, 3 wire DIN, Repeatability: ± 0.2% of full scale (± 0.6°F) wire via quick disconnect fitting (Style 1) Ambient Operating Limits: 40 to 140°F (4.4 to 60°C) Display Update: 3 seconds Ambient Temp. Stability: Better then 0.1°C per 10°C ambient shift Calibration Adjustment: Via onboard switches 32 to 140°F (0 to 65°C) Storage Temp.: Display: LCD: 4 digit main display, 6 digit secondary; 0.9" high contrast LCD **Order Information** FIJ **REMOTE DISPLAY CABLE LENGTH** STYLE None 0 0 Standard Thermometer 5 5' (style 5) 1 Thermometer w/ Optional RTD 10' (style 5) 6 Thermometer w/Dual Switches(DC power /SPST)² 2 15' (style 5) 7 **Remote Display Thermometer** 5 8 20' (style 5) (must order mounting style 9) **CABLE LENGTH** DISPLAY UNITS None (style 0, 2 ³ or 5) 00 0 Deg F 10' (style 1, 2 or 2 w/AC module) 02 1 Deg C 04 20' (style 1, 2 or 2 w/AC module) 06 30' (style 1, 2 or 2 w/AC module) MOUNTING 40' (style 1, 2 or 2 w/AC module) 08 Bottom 1 50' (style 1, 2 or 2 w/AC module) 75' (style 1, 2 or 2 w/AC module) 10 Back (90° elbow) 4 15 Α Back (90° adjustable elbow) 100' (style 1, 2 or 2 w/AC module) 20 5 Left 6 Right PROBE 7 Top Standard probe 0 8 Back (45° elbow) (choose for projectile well fittings) Remote Display - Bottom Cable Exit 9 1 Heavy duty probe 1 FITTING/INSERTION (recommended for lengths over 6") 001-013 1/2" Tri-Clamp^{® 6} 002-037 3/4" Tri-Clamp[®] 1-1/4" 2-3/4" 004-037 1-1/2" Tri-Clamp® 2-3/4" 005-049 2" Tri-Clamp® 3-1/2" 062-139 Projectile Well(41247) 5 063-161 Projectile Well(41280) 3-1/2" 9-1/8" 2-1/2" Tri-Ċlamp® 006-049 10-1/2" 3" Tri-Clamp® 007-053 3-3/4" Projectile Well(41279)^{4,5} 008-065 4" Tri-Clamp® 4-1/2["] 064-187 12-1/8" 010-031 1-1/2" APC "K" ⁴ 011-730 2" APC "K" ⁴ Bi-Metal Well 1/2" NPT 5 Bi-Metal Well 1/2" NPT 5 084-033 2-3/8" 2-1/2" 084-057 4" 2-25/32" Well fittings not 016-031 1-1/2" Cherry-Burrell "I" 084-089 Bi-Metal Well 1/2" NPT 5 6" 2-3/8" electropolished Bi-Metal Well 1/2" NPT 5 9" 017-730 2" Cherry-Burrell "I" 2-25/32" 084-137 Bi-Metal Well 1/2" NPT 4, 5 12" 1-1/2" G&H "H" Line (male) 084-185 027-044 3 3/16" Bi-Metal Well 1/2" NPT 4,5 3-15/16" 15" 028-056 2" G&H "H" Line (male) 084-233 Bi-Metal Well 1/2" NPT 4,5 1-1/2" Cherry "Q 084-281 18" 2-1/2" 032-033 084-377 Bi-Metal Well 1/2" NPT 4,5 3-1/2" 24" 033-049 2" Cherry "Q' 1-1/2" #14 Bevel Seat 044-029 (with 13 H nut) 2-1/4" 2-5/8" 045-035 2" #14 Bevel Seat (w/ nut) 4 Heavy Duty Probes with 3/4"Dia., insertion lengths from 3-1/2" to 43-1/2" Mounting available for standard fittings, Tri-Clamp®, Cherry "I", Bevel Seat and Umbrella Consult factory for other fittings. Α For AC Relays, order remote relay module# PM0606004 Style 2 supplied with 90° Field Wireable Connector, no cable Sensors with these options are non-cancellable/non-returnable for credit. 5 Meets 3-A when used with a 3-A compliant well 6 Not 3-A Compliant 05056/2.1/2016-03-21/GR/NA ANDERSON INSTRUMENT COMPANY Phone 800-833-0081 Tech. Support:

ANDERSON INSTRUMENT COMPAN 156 Auriesville Road Fultonville, NY 12072 Fax 518-922-8997 info@anderson-negele.com Tech. Support: techservice@anderson-negele.com Phone 800-833-0081